

Philips Consumer Lifestyle

eManual

PRODUCT INFORMATION

- · This product meets the requirements regarding interference suppression on radio and TV.
- After the product has been repaired, it should function properly and has to meet the safety requirements as officially laid down at this moment.

TECHNICAL INFORMATION

 Colour : Valentine red • Power consumption : 2000 W • Suction Power : 340 W Noise level : < 82 dBA · Action radius : II mtr Cord length : 8 m

 Filtration : Power cylone

Hepa 12 Super Clean Air

: 505 x 292 x 292 mm • Dimensions appliance • Dimensions F-box : 650 x 330 x 310 mm

 Weight : 5.5 kg

ACCESSORIES

 Nozzle : Tai Chi all purpose nozzle Special nozzle : Super parquet nozzle

 Tubes : Metal lacquered 2 pcs. telesc. tube

 Accessories : Crevice nozzle, Small nozzle

and Brush

· Accessory storage : Accessory clip on tube

 Coupling : Button coupling

REPAIR INSTRUCTION

· No specific issues

OPTIONAL (accessories)


· No specific issues






DISASSEMBLY- AND RE-ASSEMBLY ADVISE


• To remove the Bucket, unlock the top handle by pushing the button on the lid of Bucket (see picture).



 The button (3) on the lid is a spare part, it can be replaced by removing screw A (see picture).




- The bucket can only be placed back with the lid mounted and positioned in the correct way, otherwise the handle cannot be closed.
- The Inlet filter assy (4) on the front (motor side) of the Bucket can be removed by pulling the lip at the top (see picture).



The foam in the Inlet filter assy can be cleaned.
 By pulling the plastic ring the foam filter can be removed without touching the dirt on the filter (see picture).


FC8768/01



• The bottom of the Bucket can be removed as shown in the picture below.

Remark:


The Bucket can be placed back without the bottom, this will not lead to a safety problem, but all the dust will get into the bottom housing.




To reach the inner parts for repair, Upper housing (18) has to be removed. First the On/Off button (17) and Cordwinder button (16) must be removed, this can be done with a screwdriver.


Remark:


The two buttons are secured with 4 "snap locks", be careful when removing (see picture).






• When lifting at position **b** push the button a little towards the front side.







• When assembling, the buttons can easily be mounted by clicking, start at the side of the handle.


Remark:


Check that the two springs are in the correct position.

DISASSEMBLY- AND RE-ASSEMBLY ADVISE


FC8768/01

- After removing the two buttons remove the 4 screws
 B at the back and the 5 screws C at the front of the Upperhousing (see pictures).
- Screw D at the front does not need to be removed, this screw is for ESD and is located in the Lowerhousing.






• To replace the potmeter (9) situated at the bottom of the upperhousing, remove knob (7) on top of the upperhousing and remove the 2 scews E at the bottom of the upperhousing (see picture).




After removing the Upperhousing, Hose connection (10) and Bucket inlet sealing (13) are accessible. To replace the Hose connection screw F has to be removed.




 To replace Cordwinder (24) or Motor (31) Motor housing (28) has to be removed, this can be done by removing the 4 screws G (see picture).

Remark:

A special long screw driver is needed!



• To replace the PCB (9) remove the 2 short screws H.



Pos	Service code	Description	Remark
1* 2* 3 4 5	9965 100 51329 9965 100 51299 9965 100 51311 4322 005 33151 9965 100 51318	Bucket assy Lid assy Unlock button Inlet filter assy Exhaust grille assy	Smoke bl. transp. / Met. silver Smoke bl. transp. / Met. silver Deep black
6 7 8 9	4322 004 93711 9965 100 51319 9965 100 51312 4322 006 24702 9965 100 51305	HEPA filter 12 Cougar Turn knob Decorative ring PCBA Cougar Hose connection	Deep black Deep black Deep black
11 12 13 14	9965 100 51306 9965 100 51324 9965 100 51308 9965 100 51323 9965 100 51322	Inlet sealing Caster assy Bucket inlet sealing Cordwinder lever Top handle assy	Deep black Deep black / Met. silver
16 17 18 19 20	9965 100 51297 9965 100 51301 9965 100 51368 9965 100 51327 9965 100 51321	CW button On/Off button Upper housing Protection ring (on switch) Cord outlet assy	Deep black Deep black Valentine red Metallic 20849 Deep black
21 22 23 24 25	9965 100 51325 9965 100 51326 9965 100 51302 4322 005 33171 9965 100 51303	Handle pushing tube Handle pushing tube spring Valve assy Cordwinder Cougar Lower housing	8 m / 4.8 plug Deep black
26 27 28 29 30	9965 100 51313 9965 100 51316 9965 100 61664 9965 100 51304 9965 100 51317	Motor housing cover Exhaust sealing Motor housing Silencer motor housing Motor sealing ring	
31 32 33 34 35	4322 006 99041 9965 100 51296 9965 100 51315 9965 100 51314 9965 100 51328	Domus 230 V / 50 Hz 1800 W IEC Motor silencer Silencer lower housing Motor housing sealing Motor buffer back	CCAW Wire
36 37 38 39 40	4322 003 46561 4322 004 24561 4322 004 24071 4322 004 24061 4322 003 42561	Rear wheel assy High end Hose assy Cougar Telescopic Tube Actuator bush Taichi nozzle Accessory clip	Met. silver / Ink black Dark raven Dark raven Dark raven
41 42 43 44	4322 004 24221 4322 004 24161 4322 004 24181 4322 004 24591	Crevice nozzle Small nozzle Plumeau assy Super parquet nozzle Standard	Dark raven Dark raven Dark raven Dark raven

 $^{{}^*}$ Standardized colour

